


HEMT MMIC Driver Amplifier, 25-30GHz

The **P35-5126-000-200** is a high performance 25-30GHz Gallium Arsenide driver amplifier. This product is intended for use in fixed-point microwave systems and satellite communications.

The die is fabricated using Bookham Technology's 0.20 μ m gate length, pHEMT process and is fully protected using Silicon Nitride passivation for excellent performance and reliability.

Features

- Over 22dBm Output Power @ 28GHz
- 10dB Gain from 25 to 30GHz
- Small Die Size (2 x 1mm)



Electrical Performance





Ambient Temperature $22 \pm 3^\circ \text{C}$, $Z_0 = 50\Omega$, $V_{dd} = 4\text{V}$, V_{g1} set for $I_{d1}=50\text{mA}$, V_{g2} set for $I_{d2}=90\text{mA}$ Unless otherwise stated

Parameter	Conditions	Min	Typ	Max	Units
Small Signal Gain	25 – 30GHz	-	10	-	dB
Gain slope	25 – 30GHz	-	± 0.5	-	dB
Input Return Loss	25 – 30GHz	-	10	-	dB
Output Return Loss	25 – 30GHz	-	10	-	dB
Output power at 1dB gain compression	28GHz, $V_{dd} = 5\text{V}$	-	22	-	dBm
First Stage Current	By Adjustment of V_{g1}	-	50	-	mA
Second Stage Current	By Adjustment of V_{g2}	-	90	-	mA
Thermal Resistance	-	-	130	-	$^\circ\text{C/W}$

Notes


1. All parameters measured on wafer

Typical RFOV Performance (----- With Bondwires)




Typical RFOV Performance


Output Power @ 1dB Compression




Pout vs Pin (4V)




Gain vs Pin (4V)




Current vs Pin (4V)




PAE vs Pin (4V)




Pout vs Pin (5V)




Gain vs Pin (5v)



Current vs Pin (5v)




PAE vs Pin (5v)



Frequency		S11		S21		S12		S22	
(GHz)	Mag	Angle	Mag	Angle	Mag	Angle	Mag	Angle	
20.00	0.66	-49.9	2.78	162.6	0.003	76.5	0.13	-144.1	
20.25	0.67	-53.3	2.87	151.5	0.003	71.8	0.14	-142.9	
20.50	0.67	-56.9	2.95	140.8	0.003	67.1	0.15	-142.4	
20.75	0.67	-60.5	3.02	130.3	0.003	53.2	0.15	-142.0	
21.00	0.67	-64.5	3.09	119.9	0.003	48.3	0.16	-142.3	
21.25	0.67	-68.6	3.14	109.7	0.003	41.1	0.17	-143.4	
21.50	0.67	-72.6	3.17	99.8	0.003	30.4	0.18	-145.4	
21.75	0.66	-76.6	3.21	90.2	0.003	29.1	0.19	-147.1	
22.00	0.65	-80.7	3.25	80.7	0.004	20.7	0.19	-149.1	
22.25	0.64	-84.8	3.28	71.2	0.003	14.7	0.20	-151.4	
22.50	0.62	-88.7	3.31	61.8	0.003	6.8	0.20	-154.0	
22.75	0.60	-92.8	3.33	52.4	0.003	-4.2	0.21	-156.5	
23.00	0.58	-96.2	3.34	43.1	0.003	-12.2	0.21	-159.1	
23.25	0.56	-99.8	3.36	33.9	0.003	-5.1	0.22	-161.6	
23.50	0.54	-103.2	3.36	24.7	0.003	-18.2	0.22	-164.6	
23.75	0.52	-106.4	3.37	15.6	0.003	-19.6	0.22	-167.1	
24.00	0.49	-109.5	3.36	6.5	0.003	-30.2	0.22	-170.0	
24.25	0.47	-112.4	3.35	-2.3	0.003	-37.5	0.22	-172.7	
24.50	0.45	-114.9	3.34	-11.0	0.003	-45.2	0.22	-175.2	
24.75	0.42	-117.6	3.33	-19.7	0.003	-47.9	0.22	-178.0	
25.00	0.40	-119.9	3.32	-28.3	0.002	-47.7	0.22	179.2	
25.25	0.37	-122.3	3.32	-37.0	0.003	-54.0	0.22	176.2	
25.50	0.35	-124.3	3.31	-45.5	0.003	-73.0	0.22	173.3	
25.75	0.32	-125.7	3.31	-54.0	0.003	-84.0	0.22	170.8	
26.00	0.30	-127.1	3.32	-62.4	0.003	-87.6	0.22	168.3	
26.25	0.28	-128.3	3.32	-70.8	0.003	-92.2	0.22	166.0	
26.50	0.25	-129.2	3.34	-79.5	0.003	-104.2	0.22	163.2	
26.75	0.23	-129.6	3.35	-88.2	0.004	-111.7	0.22	160.5	
27.00	0.21	-129.7	3.38	-96.9	0.004	-123.0	0.21	158.1	
27.25	0.19	-129.4	3.41	-105.6	0.004	-143.7	0.21	156.5	
27.50	0.16	-128.4	3.45	-114.6	0.004	-151.9	0.21	154.6	
27.75	0.13	-125.8	3.51	-123.9	0.004	-163.3	0.22	152.5	
28.00	0.11	-119.5	3.57	-133.5	0.004	-172.5	0.22	149.8	
28.25	0.08	-105.6	3.62	-143.4	0.004	-166.1	0.23	147.1	
28.50	0.07	-79.5	3.69	-153.6	0.004	-177.9	0.23	144.9	
28.75	0.09	-52.8	3.75	-164.5	0.005	172.6	0.24	141.6	
29.00	0.12	-36.7	3.81	-175.9	0.004	153.8	0.25	137.2	
29.25	0.16	-29.1	3.86	172.3	0.004	157.1	0.26	133.2	
29.50	0.21	-27.2	3.89	159.8	0.005	151.4	0.27	129.4	
29.75	0.27	-27.6	3.88	146.4	0.005	138.1	0.28	124.8	
30.00	0.33	-30.6	3.82	132.4	0.005	121.4	0.29	119.9	
30.25	0.40	-34.8	3.70	117.9	0.006	110.7	0.30	114.0	
30.50	0.46	-40.0	3.51	103.2	0.006	103.9	0.32	107.5	
30.75	0.52	-46.0	3.24	88.5	0.007	82.5	0.33	99.9	
31.00	0.57	-52.2	2.94	74.5	0.006	74.7	0.33	92.9	
31.25	0.61	-58.1	2.63	61.3	0.006	65.1	0.33	86.2	
31.50	0.65	-63.6	2.33	48.9	0.005	52.4	0.33	80.0	
31.75	0.67	-68.6	2.05	37.1	0.005	52.5	0.33	73.4	
32.00	0.70	-73.3	1.79	26.1	0.004	39.2	0.32	67.8	

Chip Outline



Die size:	2.05 x 1.14mm
RF bond pads (1 & 2):	80μm x 120μm
All other bond pads:	120μm x 120μm
Die Thickness:	100μm

Pad Details

Pad	Function
1	RF Input
2	RF Output
3	Gnd
4	Vd2
5	N/C
6	Vg2
7	Vd1
8	N/C
9	Vg1
10	Gnd

Handling and Assembly Information

Gallium Arsenide (GaAs) devices are susceptible to electrostatic and mechanical damage. Dice are supplied in antistatic containers, which should be opened in cleanroom conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickups or, with care, sharp tweezers.

GaAs Products from Bookham Technology's H40P Foundry process are 100μm thick and have through GaAs vias to enable grounding to the circuit. Windows in the surface passivation above the bond pads are provided to allow wire bonding to the die.

The surface to which the die are to be attached should be cleaned with a proprietary de-greasing leaner. Eutectic mounting should be used and entails the use of a gold-tin (AuSn) preform, approximately 0.001" thick, placed between the die and the attachment surface. The preferred method of mounting is the use of a machine such as a Mullins 8-140 die bonder. This utilises a heated collet and workstation with a facility for applying a scrubbing action to ensure total wetting and avoid the formation of voids. Dry nitrogen gas is directed across the work piece.


The gold-tin eutectic (80% Au 20% Sn) has a melting point of approximately 280°C (Note: Gold Germanium with a higher melting temperature should be avoided, in particular for MMICs). The work station temperature should be 310°C ± 10°C. The collet should be heated, and the die pre-heated to avoid excessive thermal shock. The strength of the bonding formed by this method will result in fracture of the die, rather than the bond under die strength testing.

The P35-5126-000-200 amplifier die has gold bond pads. The recommended wire bonding procedure uses 25μm (0.001") 99.99% pure gold wire with 0.5-2% elongation. Thermo-compression wedge bonding is preferred though thermosonic wire bonding may be used providing the ultrasonic content of the bond is minimised. A work station temperature of 260°C ± 10°C with a wedge tip temperature of 120°C ± 10°C is recommended. The wedge force should be 45 ± 5 grams. Bonds should be made from the bond pads on the die to the package or substrate.

The RF bond pads at the input and output are 80μm x 120μm; all other bond pads are 120μm x 120μm. The P35-5126-000-200 has been designed to include the inductance of a single 0.2mm length of 25μm bond wire at both the input and output, facilitating the integration of the die into a 50Ω environment.

Operating and Biasing of the P35-5126-000-200

The P35-5126-000-200 is a two-stage amplifier. The drain bias for both stages (Vd1 & Vd2) should be set to 4.0 volts. The gate voltages (Vg1 & Vg2) are typically set to -0.3V(50% Idss) to give an Id1 of 50mA and Id2 of 90mA. The separate drain and gate voltage supplies for both stages can be combined into single supplies (Vdd & Vgg). DC bias supplies should be decoupled to ground using 100pF chip capacitors placed close to the chip with short bondwires to the amplifier bond pads.

Typical bonding detail*Absolute maximum Ratings*

Max Vdd	+7V
Max Vgg	-2V
Max channel temperature	150°C
Storage temperature	-65°C to +150°C

Ordering Information

P35-5126-000-200



Thinking RF solutions

MMICS

Bookham Technology plc
 Caswell
 Towcester
 Northamptonshire
 NN12 8EQ
 UK

• Tel: +44 (0) 1327 356 789

• Fax: +44 (0) 1327 356 698

rfsales@bookham.com**Important Notice**

Bookham Technology has a policy of continuous improvement. As a result certain parameters detailed on this flyer may be subject to change without notice. If you are interested in a particular product please request the product specification sheet, available from any RF sales representative.



22735